


# InnoVfoam

## AFFF 860



### **Description**

InnoVfoam AFFF 860 is an aqueous film forming foam concentrate (AFFF) consisting of fluorocarbon and hydrocarbon surfactants blended with various solvents, preservatives and stabilisers. The foam forms an aqueous film that rapidly cuts off the oxygen supply and thus knocks down the fire. The expanded foam from which the film is drained forms a stable blanket that suppresses the release of flammable vapours and cools down the fuel surface extinguishing the fire and preventing re-ignition.

The low surface tension of the water foam concentrate solution enables the aqueous film, although heavier than the burning liquid, to float on top of the liquid surface. InnoVfoam AFFF 860 should be used at 6% proportioned solution (6 part concentrate in 94 parts of water) in fresh or seawater. It may also be stored as a pre mix solution in fresh water.

### **Application**

InnoVfoam AFFF 860 is intended for use on class B hydrocarbon fuel fires such as oil, diesel and aviation fuels. It can be used with both aspirating and non-aspirating discharge devices. InnoVfoam AFFF 860 is especially suited whenever rapid fire knockdown is essential. It is compatible with all dry chemical powders and can be used in powder/foam twin agent systems.

### **Fire performance & foaming**

The fire performance of InnoVfoam AFFF 860 has been tested and documented according to the UK Ministry Of Defence Standard 42/40 and EN 1568 Part 3 at 6% proportioning. Foaming index no less than 7:1 (normally 8:1). 25% drainage time 3.0 minutes (normally 3.5).


### **Storage/Shelf life**

Stored in original unbroken packaging the product will have a long shelf life. The recommended storage temperature range of InnoVfoam AFFF 860 is from -14°C to 55°C. Freezing and thawing will have no impact on the performance. Synthetic foam concentrates should only be stored in stainless steel or plastic containers. Since electromagnetic corrosion can occur at joints between different metals when they are in contact with foam concentrate, only one type of metal should be used for pipelines, fittings, pumps, and tanks employed in the storage of foam concentrates.



# InnoVfoam

## AFFF 860



### Proportioning

InnoVfoam AFFF 860 can easily be proportioned at the correct dilution using conventional equipment such as:

- Inline inductors
- Balanced pressures, variable flow proportioning systems
- Bladdertanks
- Around the pump proportioning systems
- Water turbine driven foam proportioners
- Self inducing branch pipes and nozzles.



### Technical data

<b>Appearance</b>	Clear Amber Liquid
<b>Specific gravity @ 20° C</b>	1.02 +/- 0.01 g/ml
<b>Viscosity approx @ 20° C</b>	<10 cSt
<b>pH</b>	7.5 +/- 1.0
<b>Freezing point</b>	-15 ° C
<b>Pour point</b>	-14 ° C
<b>Suspended sediment (v/v)</b>	Less than 0.2%
<b>Surface tension approx</b>	20.0 dynes/cm

### Packaging

We supply InnoVfoam in 25 litre cans and 200 litre drums. We can also ship in 1000 litre containers or in bulk.

### International Approvals

- EN 1568 part 3