



DECON/pak

DECON/PAK METRIC 2.5" BICM

UM45-BIC-D

45 LPM @ 7 BAR ENGLISH TEXT

\$795.00 Guaranteed US Price

FEATURES

The DECON/pak Portable Decontamination System is a self-contained agent proportioning and rinse application system developed specifically for gross decontamination of firefighting personnel and equipment. Inject a variety of approved personal protective clothing gross decontamination agents from 0.1% to 0.5% The rugged green polypropylene 9.5 l (2.5 gal.) concentrate tank is supplied by a pressurized 25 or 38 mm (1 or 1 1/2") hoseline. The unit includes an integrated twist shut-off valve, selective injection metering knob, and is easily disassembled for cleaning. The pressure vacuum seal on the lid and inlet debris screen assure that the approved decontamination agent chosen can be stored ready for immediate use. A detachable fan spray nozzle is attached to a 3.7 m (12') discharge hose for ease of use during agent application or rinsing operations.

SPECIFICATIONS

Flow Rate	45 l/min
Inlet Coupling Swivel	Full Time Swivel
Pressure	100 psi (7 bar)
Valve Actuation Method	Rotational
Valve Design	Aluminum Slide Valve
Weight	15

DOCUMENTS

Instructions For Installation, Safe Operation and Maintenance
[DECON/PAK PORTABLE DECONTAMINATION SYSTEM \(PDF\)](#)

Product Brochures
[DECON/PAK PORTABLE GROSS DECONTAMINATION SYSTEM \(PDF\)](#)

Online Videos
[DECON/PAK PORTABLE GROSS DECONTAMINATION SYSTEM \(MP4\)](#)

ABOUT THE DECON/PAK

The DECON/pak Portable Decontamination System is a self-contained agent proportioning and rinse application system developed specifically for gross decontamination of firefighting personnel and equipment. Injecting a variety of approved PPE gross decontamination cleaning agents from 0.1% to 0.5%, the rugged green 2.5 gal. (9.5 l) concentrate tank is supplied by a pressurized 1" or 1 1/2" (25 or 38 mm) hoseline.

The unit includes an integrated twist shut-off valve, selective injection metering knob, and is easily disassembled for cleaning. The pressure vacuum seal on the lid and inlet debris screen assure that the approved decontamination agent chosen can be stored ready for immediate use.